

DEMINTECH



30 years of experience
Domestic water treatment
and industrial.

Description:

DEMINTECH provides distillate-equivalent water of excellent purity using the process ion exchange. Calcined residue less than 1mg / l for an electrical conductivity less than $1\mu\text{S} / \text{cm-l}$.

Conductivity meter:

Needle conductivity meter measuring range from 0 to $50\mu\text{S}$. Power supply 230 V.

Cartridge:

Made of fiberglass reinforced polyethylene. Delivery possible in 10 - 30 - 50 liters.

Flexible:

3/4 F connection. Length 150 cm.

Advantage:

No regeneration.
Simplicity compared to cartridges to regenerate.
Water equivalent to distillate always available by simple change of used cartridges.

Capacity:

For a 10 Liters: about 650 Liter at $0\mu\text{S} / \text{cm}$ at 20°C for an entry at $750\mu\text{S} / \text{cm}$.

Various jobs:

The use of demineralised water is varied; it does not extend only to processes conventional chemicals and techniques but increasingly in other areas. Medical technology, laboratories, air conditioning, laundries, service stations, pharmaceutical industry, cosmetics, batteries, chemist, photo labs, horticulture and florist, orchid grower, aquarium. These areas of use are just some examples for the use of DEMINTECH



Rue de la Cale Sèche 34 - 4684 Haccourt | BELGIUM
Tél. : 0032 (0)4 374 25 00 | www.water-tech.be

